



C-MAG HS 10 digital

/// Data Sheet

Magnetic stirrer with heating and ceramic heating plate which offers excellent chemical resistance.

- Powerful motor for stirring quantities of up to 15 I (H2O)
- Simultaneous digital display of target and actual temperatures via LCD dispaly
- Directly connection for a PT 1000 temperature sensor enable a precise temperature control (included in delivery)
- Control accuracy in medium +/- 0,5 K (in combination with PT 1000)
- Display of actual temperature value in medium with 0,1 K resolution when using PT 1000 temperature sensor
- 3 operating modes to choose (standard, safe, adjustment protection)
- Fixed safety circuit of 550 °C

www.ika.com Subject to technical changes



- Hot Top indicator >> hot surface warning to prevent burns!
- Digital error code display
- Elevated control panel for protection against leaking liquids

Technical Data

Number of stirring positions	1
Stirring quantity max. per stirring position (H2O) [I]	15
Motor rating output [W]	1.5
Speed control	scale 0 - 6
Speed range [rpm]	100 - 1500
Stirring bar length max. [mm]	80
Heat output [W]	1500
Heating temperature range [°C]	50 - 500
Heat control	stepless
Heating rate heating plate [K/min]	5
Connection for ext. temperature sensor	PT1000
Fixed safety circuit [°C]	550
Set-up plate material	ceramic
Set-up plate dimensions [mm]	260 x 260
Dimensions (W x H x D) [mm]	300 x 105 x 415
Weight [kg]	6
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	230 / 120 / 100
Frequency [Hz]	50/60
Power input [W]	1520